


BA NiTi Endo Contra-Angle



KEY FACTS:

- Endodontic contra-angle with torque control that doesn't require a table top unit, direct connection to the motor.
- 2 models available: BAE35 115:1 speed reducing handpiece for electric micromotors, and BAE45 66:1 speed reducing handpiece for air motors.
- Can be used with all the common NiTi files in the market.
- Easy torque setting with the unique magnetic ring (5 torque levels).
- Retro-rotation system prevents the file from getting jammed in the root and any excessive torque.
- Optional apex clip connection.

1. BA NITI


| Code | Description |
|----------|-------------------------|
| A. BAE35 | 115:1 Endo contra-angle |
| B. BAE45 | 66:1 Endo contra-angle |

2. BA Clip

| Code | Description |
|---------|---------------------------------|
| BAE35C1 | 2mm Clip For BA NiTi endo c/a |
| BAE35C2 | 1.5mm Clip For BA NiTi endo c/a |

BA Optima E+

Compact and ergonomic, simple to use table top endodontic motor.



KEY FACTS:

- Auto reverse function.
- Useable on battery for up to 5 hours or with supplied adaptor.
- Reducing gear ratio up to 16:1.
- Torque control from 0.6 to 5.2N.cm.
- 9 programs.
- Foot control and handpiece stand included.
- Two motor types available.
- Maximum speed of motor: 13,000rpm.
- Includes handpiece/head.

BA Optima E+ Endodontic Motor

| Code | Description |
|-----------|---|
| A. BAE300 | Complete unit with A-type motor (BAE05) |

BA Optima E+

| Code | Description |
|-----------|---|
| B. BAE350 | Complete unit with E-type motor (BAE15) |

BA Optima E+ Endo Head

| Code | Description |
|----------|----------------------------|
| C. BAE05 | Endo head for A-type motor |

BA Optima E+ Endo Contra-Angle

| Code | Description |
|----------|---|
| D. BAE15 | Endo contra-angle head for E-type motor |