

traus ENDO

Cordless Endo Motor

- Optimized Design for user Interface
- Ergonomic and compact body
- Suitable for use with most major brands of Ni-Ti files



Standard gear ratio 20:1



5 memory programs



Quick Charging 2.5 hours




8.5 hours Using time




Auto Reverse

Functions




Auto-Reverse Function

1 Auto Stop



2 Auto Reversing



Specification

Charger (TRAUS XEW10)

Rated Voltage	AC 100-240 V, 50/60 Hz
Output	DC 4 V
Charging Time	approx. 2.5 hours
Using Time	approx. 8.5 hours

Contra Angle Handpiece

	Standard		
	ACL(B) - 41EP	ACL(B) - 42EP	ACL(B) - 46EP
Gear Ratio	20 : 1	16 : 1	10 : 1
Weight	35g	35g	34.8g

Motor Handpiece (TRAUS MCE10XX)

Rotation Speed (min)	Gear Ratio	Torque Level (N-cm)	Rated Voltage
200~999	10 : 1	1.0 - 3.0	2.5 V
100~600	16 : 1	1.0 - 4.0	
100~600	20 : 1	1.0 - 4.0	